

R63 Reflector 5.5W (40W) 3000K 420lm E27 Non-Dimmable Lamp*Quick Order Code: 29-92-35 / Page: 1*

This 5.5W retrofit Integral LED R63 delivers brightness similar to a 40W incandescent bulb, in warm white light. It features a 420 lumen output, multi Everlight LEDs and an anti-glare refractor. Ideal for living rooms, dining rooms, bathroom and bedrooms, in classic or modern wall lamp fittings.

Product Details

Partcode: ILR63E27O5.5N03KNENA

Quick Order Code: 29-92-35

Range Name: Convexo

Product Type: Reflector

Warranty: 3 Years

CE / RoHS: Yes

Physical Data

Lamp Base: E27

Base Type: Edison screw

Base Colour: Matt white

Globe Type: Reflector R63

Globe Finish: Frosted

Material: Aluminium, Polycarbonate

Construction: Plastic heat-sink, Plastic diffuser

Physical Data

Length: 106mm
Width: 63mm
Weight (Unpackaged Single Unit): 70g
Lamp or Luminaire Shape: Round
Lamp Fixing: Pendant

Electrical Data

Voltage Range: 220-240V
Power Consumption: 5.5 Watts
Driver included: Yes
Driver IC Manufacturer: Silergy
Electric Current: AC
Ampage: 39.00mA
Frequency Range: 50 Hz
Power Factor: ≥ 0.60
Wattage Equivalent: 40 Watts
Dimming: Non-dimmable
LVD Certified: Yes
EN: EN-62560

Light Data

Lumens: 420lm
Lumens per Watt: 76.0lm/W
Beam Angle: 120°
Correlated Colour Temperature (CCT): 3,000k
Colour Temperature: Warm White
Colour Rendering Index (CRI): ≥ 80
LED Manufacturer: Everlight
LED Type: Surface mounted device (SMD)
Instant on - Less than 1 second: Yes
Lifetime: 25,000 hrs
Switching Cycles: $>12,500$ X

Environmental

Energy Rating: A+

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788206330

Packaged Weight (Unit of 1): 108g

Length (unit of 1): 124mm

Width (unit of 1): 67mm

Depth (unit of 1): 67mm

Outer packaging info available on website

Product data last updated on: Tuesday, September 23, 2014 - 15:31