

Classic Globe (GLS) 6.3W (40W) 2700K 470lm E27 Non-Dimmable Frosted Lamp

Quick Order Code: 50-02-50 / Page: 1

**Product Details**

Partcode: ILA60E27O6.3N27KBEWA

Quick Order Code: 50-02-50

Range Name: Mensae

Product Type: Classic Globe (GLS)

Warranty: 3 Years

CE / RoHS: Yes

Physical Data

Lamp Base: E27

Base Type: Edison screw

Base Colour: Matt white

Globe Type: Classic Globe (GLS)

Globe Finish: Frosted

Material: Plastic, Polycarbonate, Nickel plated brass

Construction: Aluminium and Plastic heat-sink, Injection moulded diffuser

Physical Data

Length: 110mm
Width: 60mm
Weight (Unpackaged Single Unit): 54g
Lamp or Luminaire Shape: Round

Electrical Data

Voltage Range: 220-240V
Power Consumption: 6.3 Watts
Driver included: Yes
Driver IC Manufacturer: Silergy
Electric Current: AC
Ampage: 51.00mA
Frequency Range: 50 Hz
Power Factor: ≥ 0.50
Wattage Equivalent: 40 Watts
Dimming: Non-dimmable
LVD Certified: Yes
EN: EN-62560

Light Data

Lumens: 470lm
Lumens per Watt: 75.0lm/W
Beam Angle: 240°
Correlated Colour Temperature (CCT): 2,700k
Colour Temperature: Warm
Colour Rendering Index (CRI): ≥ 80
LED Manufacturer: Seoul
LED Type: Surface mounted device (SMD)
Instant on - Less than 1 second: Yes
Lifetime: 25,000 hrs
Switching Cycles: $>12,500$ X

Environmental

Energy Rating: A+

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788208099

Packaged Weight (Unit of 1): 92g

Length (unit of 1): 123mm

Width (unit of 1): 68mm

Depth (unit of 1): 68mm

Outer packaging info available on website

Product data last updated on: Friday, October 3, 2014 - 13:27