

Classic Globe (GLS) 12W (75W) 5000K 1200lm B22 Non-Dimmable Frosted Lamp

Quick Order Code: 85-25-64 / Page: 1

**Product Details**

Partcode: ILA60B22O12N05KBKWA

Quick Order Code: 85-25-64

Range Name: Mensae

Product Type: Classic Globe (GLS)

Warranty: 3 Years

CE / RoHS: Yes

Physical Data

Lamp Base: B22

Base Type: Bayonet cap

Base Colour: Matt white

Globe Type: Classic Globe (GLS)

Globe Finish: Frosted

Material: Aluminium, Polycarbonate, Nickel plated brass

Construction: Aluminium and Plastic heat-sink, Injection moulded diffuser

Physical Data

Length: 125mm
Width: 60mm
Weight (Unpackaged Single Unit): 148g
Lamp or Luminaire Shape: Round

Electrical Data

Voltage Range: 220-240V
Power Consumption: 12.0 Watts
Driver included: Yes
Driver IC Manufacturer: Silergy
Electric Current: AC
Ampage: 104.00mA
Frequency Range: 50 Hz
Power Factor: ≥ 0.50
Wattage Equivalent: 75 Watts
Dimming: Non-dimmable
LVD Certified: Yes
EN: EN-62560

Light Data

Lumens: 1,200lm
Lumens per Watt: 100.0lm/W
Beam Angle: 240°
Correlated Colour Temperature (CCT): 5,000k
Colour Temperature: Cool White
Colour Rendering Index (CRI): ≥ 80
LED Manufacturer: Everlight
LED Type: Surface mounted device (SMD)
Instant on - Less than 1 second: Yes
Lifetime: 25,000 hrs
Switching Cycles: $>12,500$ X

Environmental

Energy Rating: A+

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788208518

Packaged Weight (Unit of 1): 188g

Length (unit of 1): 140mm

Width (unit of 1): 68mm

Depth (unit of 1): 68mm

Outer packaging info available on website

Product data last updated on: Friday, October 3, 2014 - 13:27