

Classic Globe (GLS) 10.5W (60W) 2700K 806lm E27 Dimmable Lamp

Quick Order Code: 80-14-55 / Page: 1



As LED products produced using new technologies are used with old dimmer technology, achieving effective and smooth dimming can be challenging. For this dimmable lamp we have tested, and recommend, the dimmer detailed in the specification below.

This 10.5W retro-fit Integral LED Classic Globe (GLS) (large screw base) delivers a dimmable, warm light and brightness, similar to a 60W filament bulb. It features high output, multi Everlight LEDs, an anti-glare refractor, all finished in an aluminium and plastic, thermally efficient body. Ideal for living rooms, hallways and kitchens.

Product Details

Partcode: ILA60E27O10D27KBIWA

Quick Order Code: 80-14-55

Range Name: Mensae

Placement / Application: Indoor, General Lighting

Market Segment: Commercial indoor, Residential indoor

Product Type: Classic Globe (GLS)

Warranty: 3 Years

CE / RoHS: Yes

Physical Data

Lamp Base: E27

Base Type: Edison screw

Base Colour: Matt white

Globe Type: Classic Globe (GLS)

Globe Finish: Frosted

Material: Plastic, Aluminium, Nickel plated brass

Construction: Plastic and Aluminium heat sink, Polycarbonate diffuser

Physical Data

Length: 120mm
Width: 60mm
Weight (Unpackaged Single Unit): 100g
Lamp or Luminaire Shape: Round
Lamp Fixing: Pendant

Electrical Data

Voltage Range: 220-240V
Power Consumption: 10.5 Watts
Driver included: Yes
Driver IC Manufacturer: Power Integrations (PI)
Electric Current: AC
Ampage: 52.00mA
Frequency Range: 50 Hz
Power Factor: ≥ 0.80
Wattage Equivalent: 60 Watts
Dimming: Dimmable with compatible dimmers
Compatible Dimmer(s): Varilight JQP401W
LVD Certified: Yes
EN: EN-62560

Light Data

Lumens: 806lm
Lumens per Watt: 76.8lm/W
Beam Angle: 240°
Correlated Colour Temperature (CCT): 2,700k
Colour Temperature: Warm
Colour Rendering Index (CRI): ≥ 80
LED Manufacturer: Everlight
LED Type: Surface mounted device (SMD)
Instant on - Less than 1 second: Yes
Lifetime: 25,000 hrs
Switching Cycles: >12,500 X

Environmental

Energy Rating: A+

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788205159

Packaged Weight (Unit of 1): 140g

Length (unit of 1): 135mm

Width (unit of 1): 71mm

Depth (unit of 1): 71mm

Outer packaging info available on website

Product data last updated on: Tuesday, September 23, 2014 - 15:28