

## Classic Globe (GLS) 13W (75W) 2700K 1060lm B22 Dimmable Lamp

Quick Order Code: 50-00-52 / Page: 1



As LED products produced using new technologies are used with old dimmer technology, achieving effective and smooth dimming can be challenging. For this dimmable lamp we have tested, and recommend, the dimmer detailed in the specification below.

This 13W retro-fit Integral LED Classic Globe (GLS) (large bayonet base) delivers a dimmable, warm light and brightness, similar to a 75W filament bulb. It features high output, multi Everlight LEDs, an anti-glare refractor, all finished in an aluminium and plastic, thermally efficient body. Ideal for living rooms, hallways and kitchens.

### Product Details

Partcode: ILA60B22O13D27KBKWA

Quick Order Code: 50-00-52

Range Name: Mensae

Placement / Application: Indoor, General Lighting

Market Segment: Commercial indoor, Residential indoor

Product Type: Classic Globe (GLS)

Warranty: 3 Years

CE / RoHS: Yes

### Physical Data

Lamp Base: B22

Base Type: Bayonet cap

Base Colour: Matt white

Globe Type: Classic Globe (GLS)

Globe Finish: Frosted

Material: Plastic, Aluminium, Nickel plated brass

Construction: Aluminium heat sink, Polycarbonate diffuser

**Physical Data**

Length: 125mm  
Width: 60mm  
Weight (Unpackaged Single Unit): 150g  
Lamp or Luminaire Shape: Round  
Lamp Fixing: Pendant

**Electrical Data**

Voltage Range: 220-240V  
Power Consumption: 13.0 Watts  
Driver included: Yes  
Driver IC Manufacturer: Power Integrations (PI)  
Electric Current: AC  
Ampage: 72.00mA  
Frequency Range: 50 Hz  
Power Factor:  $\geq 0.80$   
Wattage Equivalent: 75 Watts  
Dimming: Dimmable with compatible dimmers  
Compatible Dimmer(s): Varilight JQP401W  
LVD Certified: Yes  
EN: EN-62560

**Light Data**

Lumens: 1,060lm  
Lumens per Watt: 81.5lm/W  
Beam Angle: 240°  
Correlated Colour Temperature (CCT): 2,700k  
Colour Temperature: Warm  
Colour Rendering Index (CRI):  $\geq 80$   
LED Manufacturer: Everlight  
LED Type: Surface mounted device (SMD)  
Instant on - Less than 1 second: Yes  
Lifetime: 25,000 hrs  
Switching Cycles: >12,500 X

### Environmental

Energy Rating: A+

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

### Packaging



EAN Barcode (unit of 1): 5055788205241

Packaged Weight (Unit of 1): 198g

Length (unit of 1): 135mm

Width (unit of 1): 71mm

Depth (unit of 1): 71mm

**Outer packaging info available on website**

*Product data last updated on: Tuesday, September 23, 2014 - 15:28*