

Mini Globe 3.5W (25W) 2700K 250lm B22 Non-Dimmable Frosted Lamp

Quick Order Code: 199379 / Page: 1

**Product Details**

Partcode: ILP45B22O3.5N27KBCMA

Quick Order Code: 199379

Range Name: Mensae

Product Type: Mini Globe

Warranty: 3 Years

CE / RoHS: Yes

Physical Data

Lamp Base: B22

Base Type: Bayonet cap

Base Colour: Matt white

Globe Type: Mini Globe

Globe Finish: Frosted

Material: Plastic, Polycarbonate, Nickel plated brass

Construction: Aluminium and Plastic heat-sink, Injection moulded diffuser

Physical Data

Length: 78mm

Width: 45mm

Weight (Unpackaged Single Unit): 31g

Lamp or Luminaire Shape: Round

Electrical Data

Voltage Range: 220-240V

Power Consumption: 3.5 Watts

Driver included: Yes

Driver IC Manufacturer: Silergy

Electric Current: AC

Ampage: 36.00mA

Frequency Range: 50 Hz

Power Factor: ≥ 0.50

Wattage Equivalent: 25 Watts

Dimming: Non-dimmable

LVD Certified: Yes

EN: EN-62560

Light Data

Lumens: 250lm

Lumens per Watt: 71.0lm/W

Beam Angle: 180°

Correlated Colour Temperature (CCT): 2,700k

Colour Temperature: Warm

Colour Rendering Index (CRI): ≥ 80

LED Manufacturer: Everlight

LED Type: Surface mounted device (SMD)

Instant on - Less than 1 second: Yes

Lifetime: 25,000 hrs

Switching Cycles: $>12,500$ X

Environmental

Energy Rating: A+

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788207887

Packaged Weight (Unit of 1): 55g

Length (unit of 1): 90mm

Width (unit of 1): 51mm

Depth (unit of 1): 51mm

Outer packaging info available on website

Product data last updated on: Friday, November 14, 2014 - 12:21