

**Candle 3.5W (25W) 2700K 250lm E14 Non-Dimmable Frosted Lamp**

*Quick Order Code: 27-73-33 / Page: 1*

**Product Details**

Partcode: ILB35E14O3.5N27KBCWA

Quick Order Code: 27-73-33

Range Name: Mensae

Product Type: Candle

Warranty: 3 Years

CE / RoHS: Yes

**Physical Data**

Lamp Base: E14

Base Type: Small Edison screw

Base Colour: Matt white

Globe Type: Candle

Globe Finish: Frosted

**Physical Data**

Length: 100mm  
Width: 35mm  
Weight (Unpackaged Single Unit): 27g  
Lamp or Luminaire Shape: Oval

**Electrical Data**

Voltage Range: 220-240V  
Power Consumption: 3.5 Watts  
Driver included: Yes  
Driver IC Manufacturer: Silergy  
Electric Current: AC  
Ampage: 39.00mA  
Frequency Range: 50 Hz  
Power Factor:  $\geq 0.50$   
Wattage Equivalent: 25 Watts  
Dimming: Non-dimmable  
LVD Certified: Yes  
EN: EN-62560

**Light Data**

Lumens: 250lm  
Lumens per Watt: 71.0lm/W  
Beam Angle: 280°  
Correlated Colour Temperature (CCT): 2,700k  
Colour Temperature: Warm  
Colour Rendering Index (CRI):  $\geq 80$   
LED Manufacturer: Everlight  
LED Type: Surface mounted device (SMD)  
Instant on - Less than 1 second: Yes  
Lifetime: 25,000 hrs  
Switching Cycles:  $>12,500$  X

### Environmental

Energy Rating: A+

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

### Packaging



EAN Barcode (unit of 1): 5055788207672

Packaged Weight (Unit of 1): 51g

Length (unit of 1): 115mm

Width (unit of 1): 48mm

Depth (unit of 1): 48mm

**Outer packaging info available on website**

*Product data last updated on: Friday, October 24, 2014 - 15:56*