

**Candle 3.8W (25W) 2700K 250lm B15 Non-Dimmable Clear Lamp**

*Quick Order Code: 80-61-80 / Page: 1*

**Product Details**

Partcode: ILB35B15C3.8N27KBCWA

Quick Order Code: 80-61-80

Range Name: Mensae

Product Type: Candle

Warranty: 3 Years

CE / RoHS: Yes

**Physical Data**

Lamp Base: B15

Base Type: Small Bayonet Cap

Base Colour: Matt white

Globe Type: Candle

Globe Finish: Clear

Material: Plastic, Polycarbonate, Nickel plated brass

Construction: Aluminium and Plastic heat-sink, Injection moulded diffuser

**Physical Data**

Length: 99mm

Width: 35mm

Weight (Unpackaged Single Unit): 33g

Lamp or Luminaire Shape: Oval

**Electrical Data**

Voltage Range: 220-240V

Power Consumption: 3.8 Watts

Driver included: Yes

Driver IC Manufacturer: Silergy

Electric Current: AC

Ampage: 37.00mA

Frequency Range: 50 Hz

Power Factor:  $\geq 0.50$

Wattage Equivalent: 25 Watts

Dimming: Non-dimmable

LVD Certified: Yes

EN: EN-62560

**Light Data**

Lumens: 250lm

Lumens per Watt: 66.0lm/W

Beam Angle: 230°

Correlated Colour Temperature (CCT): 2,700k

Colour Temperature: Warm

Colour Rendering Index (CRI):  $\geq 80$

LED Manufacturer: Seoul

LED Type: Surface mounted device (SMD)

Instant on - Less than 1 second: Yes

Lifetime: 25,000 hrs

Switching Cycles:  $>12,500$  X

### Environmental

Energy Rating: A+

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

### Packaging



EAN Barcode (unit of 1): 5055788207764

Packaged Weight (Unit of 1): 57g

Length (unit of 1): 115mm

Width (unit of 1): 48mm

Depth (unit of 1): 48mm

**Outer packaging info available on website**

*Product data last updated on: Friday, October 24, 2014 - 15:56*