

**Candle 6W (40W) 5000K 540lm E14 Non-Dimmable Clear Lamp**

*Quick Order Code: 60-88-17 / Page: 1*

**Product Details**

Partcode: ILB35E14C6.0N05KBEWA

Quick Order Code: 60-88-17

Range Name: Mensae

Product Type: Candle

Warranty: 3 Years

CE / RoHS: Yes

**Physical Data**

Lamp Base: E14

Base Type: Small Edison screw

Base Colour: Matt white

Globe Type: Candle

Globe Finish: Clear

Material: Plastic, Polycarbonate, Nickel plated brass

Construction: Aluminium and Plastic heat-sink, Injection moulded diffuser

**Physical Data**

Length: 112mm  
Width: 38mm  
Weight (Unpackaged Single Unit): 65g  
Lamp or Luminaire Shape: Oval

**Electrical Data**

Voltage Range: 220-240V  
Power Consumption: 6.0 Watts  
Driver included: Yes  
Driver IC Manufacturer: Silergy  
Electric Current: AC  
Ampage: 55.00mA  
Frequency Range: 50 Hz  
Power Factor:  $\geq 0.50$   
Wattage Equivalent: 40 Watts  
Dimming: Non-dimmable  
LVD Certified: Yes  
EN: EN-62560

**Light Data**

Lumens: 540lm  
Lumens per Watt: 90.0lm/W  
Beam Angle: 240°  
Correlated Colour Temperature (CCT): 5,000k  
Colour Temperature: Cool White  
Colour Rendering Index (CRI):  $\geq 80$   
LED Manufacturer: Everlight  
LED Type: Surface mounted device (SMD)  
Instant on - Less than 1 second: Yes  
Lifetime: 25,000 hrs  
Switching Cycles:  $>12,500 X$

### Environmental

Energy Rating: A+

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

### Packaging



EAN Barcode (unit of 1): 5055788208662

Packaged Weight (Unit of 1): 89g

Length (unit of 1): 125mm

Width (unit of 1): 51mm

Depth (unit of 1): 51mm

**Outer packaging info available on website**

*Product data last updated on: Friday, October 24, 2014 - 15:56*