

Candle 6W (40W) 5000K 540lm B22 Non-Dimmable Clear Lamp*Quick Order Code: 66-39-43 / Page: 1***Product Details**

Partcode: ILB35B22C6.0N05KBEWA

Quick Order Code: 66-39-43

Range Name: Mensae

Product Type: Candle

Warranty: 3 Years

CE / RoHS: Yes

Physical Data

Lamp Base: B22

Base Type: Bayonet cap

Base Colour: Matt white

Globe Type: Candle

Globe Finish: Clear

Material: Plastic, Polycarbonate, Nickel plated brass

Construction: Aluminium and Plastic heat-sink, Injection moulded diffuser

Physical Data

Length: 110mm

Width: 38mm

Weight (Unpackaged Single Unit): 73g

Lamp or Luminaire Shape: Oval

Electrical Data

Voltage Range: 220-240V

Power Consumption: 6.0 Watts

Driver included: Yes

Driver IC Manufacturer: Silergy

Electric Current: AC

Ampage: 55.00mA

Frequency Range: 50 Hz

Power Factor: ≥ 0.50

Wattage Equivalent: 40 Watts

Dimming: Non-dimmable

LVD Certified: Yes

EN: EN-62560

Light Data

Lumens: 540lm

Lumens per Watt: 90.0lm/W

Beam Angle: 240°

Correlated Colour Temperature (CCT): 5,000k

Colour Temperature: Cool White

Colour Rendering Index (CRI): ≥ 80

LED Manufacturer: Everlight

LED Type: Surface mounted device (SMD)

Instant on - Less than 1 second: Yes

Lifetime: 25,000 hrs

Switching Cycles: $>12,500$ X

Environmental

Energy Rating: A+

Lowest Operating Temperature: -20 degrees

Maximum Operating Temperature: 40 degrees

IP (Ingress Protection) Rating: IP20

Hg 0% (Mercury Free): Yes

Packaging



EAN Barcode (unit of 1): 5055788208631

Packaged Weight (Unit of 1): 97g

Length (unit of 1): 125mm

Width (unit of 1): 51mm

Depth (unit of 1): 51mm

Outer packaging info available on website

Product data last updated on: Friday, October 24, 2014 - 15:56