


Strip 12V IP67 5m x 10mm 7000K 3W/m

Quick Order Code: 76-60-59 / Page: 1



This daylight LED strip has 30 LEDs per metre and is constructed using high quality materials to ensure a consistent light and colour across the strip. This LED strip is IP67 rated and is suitable for indoor and outdoor applications. Each 5m reel is supplied with an easy-to-follow installation guide, 2x end caps (dead-end), 2x pierced end caps, 2x sets of 20cm live wires (live and neutral), 1x 45ml Silicon tube, 20x mounting clips. 3M backing tape is pre-applied to simplify the installation process. Additional accessories are available, to suit specific installation requirements.

Product Details

Partcode: ILS675M10MM07K03DABA

Quick Order Code: 76-60-59

Range Name: Acapella

Placement / Application: Decorative indoor, Water-resistant

Market Segment: Residential indoor, outdoor

Product Type: Flexible

Warranty: 3 Years

CE / RoHS: Yes

Physical Data

Base Colour: Matt white

Material: PCB and Silicon

Construction: LED surface mounted on to strip, Silicon poured on to seal

Physical Data

Length: 5m

Width: 10mm

Weight (Unpackaged Single Unit): 441g

Strip Cut Points: 100mm

Electrical Data

Voltage Range: 12V

Power Consumption Per Meter: 3.0W/m

Driver included: No

Electric Current: DC

Dimming: Dimmable with dimmable drivers and compatible dimmers

LVD Certified: Yes

EN: IEC 62031

Light Data

Lumens per Watt: 50.0lm/W

Lumens per Meter: 150lm/M

LEDs per meter: 30/m

Beam Angle: 115°

Correlated Colour Temperature (CCT): 7,000k

Colour Temperature: Daylight

Colour Type: Single

Colour Rendering Index (CRI): ≥ 75

LED Manufacturer: Chimei

LED Type: Surface mounted device (SMD)

LED Size: 35:28

Lifetime: 13,000 hrs

Environmental

Lowest Operating Temperature: -25 degrees

Maximum Operating Temperature: 60 degrees

IP (Ingress Protection) Rating: IP67

Hg 0% (Mercury Free): Yes

Packaging

EAN Barcode (unit of 1): 5055788200536

Packaged Weight (Unit of 1): 574g

Length (unit of 1): 211mm

Width (unit of 1): 260mm

Depth (unit of 1): 30mm

Outer packaging info available on website

Product data last updated on: Tuesday, September 23, 2014 - 15:28