



DC axial fans

Series 8400 NU 80 x 80 x 25 mm



Highlights:

- Motor protection against reverse polarity and locking.
- Air exhaust over struts
- Connection via 310 mm strands AWG 24, TR 64, bared and tin-plated
- Ingress protection rating of IP68

Material: Housing: Fiberglass-reinforced PBT composite
Impeller: Fiberglass-reinforced PA composite

Direction of rotation: Counterclockwise, seen on rotor

Nominal Data		Air flow	Nominal voltage	Voltage range	Sound pressure level	Sound power level	Ball bearings	Power input	Speed	Temperature range	Mass	Ingress Protection Rating	UL Approval	Curves
Type		CFM	VDC	VDC	dB(A)	Bel(A)		Watts	RPM	°C	g			
8414 NMU		34.1	24	18...28	27	4.4	Yes	1.4	2600	-20...70	95	IP68	Yes	1
8412 NU		40.6	12	8...15	32	4.7	Yes	1.7	3100	-20...70	95	IP68	Yes	2
8414 NHU		46.5	24	18...26	37	5.0	Yes	2.4	3600	-20...65	95	IP68	Yes	3

Curves

