



Polycarbonate Version Only

**UL US LISTED**

File #E65324

NEMA 4, 4X

Enclosures can be Factory Modified ( Milling, Drilling, Printing etc. )  
 Contact [mjm@hammondmfg.com](mailto:mjm@hammondmfg.com) for Quotes.  
 Solid models of this enclosure available in STEP or IGES see Web.

**NOTE**

Purchased assembly includes box, styled lid, 6 cover screws, and preformed silicone gasket.  
 General Purpose ABS version is not UL approved. (Matl UL94 - HB)  
 Polycarbonate version is UL 508 approved. (Matl UL94 - V0)

**Recommended Cover screw torque – 2.5 lbf-in (30 cN-m)**

1555VA	
1555VA Regular Enclosure	
General Purpose ABS RAL-7035	1555VAGY
Polycarbonate RAL-7035	1555VA2GY
ACCESSORIES	
Steel Inner Panels	1554VAPL
Steel Panel / P.C. Board Machine Screw [M3 x 8mm Plated]	1591MM100
Steel Panel / P.C. Board Self Tapping Screw [#6 X 1/4" (6.4mm) Plated]	1598ATS100
Cover Screws (Pkg 6) [M4 X 25mm Stainless Steel]	SC1554VA

**HAMMOND MANUFACTURING™**

**1555VA**

[www.hammondmfg.com](http://www.hammondmfg.com)