

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [130108-0088](#)  
**Status:** **Active**  
**Overview:** [Hand Lamps](#)  
**Description:** Super-Safeway™ 30W Fluorescent Hand Lamp with Cord Ballast Location and Switch, Cord Type 18/3 SJTW, Cord Length 15.24m (50.0')

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

**Agency Certification**

CSA LR85374

**General**

Product Family	Portable Lighting
Series	<a href="#">130108</a>
NEMA Configuration	NEMA 5-15
Outlet	None
Overview	<a href="#">Hand Lamps</a>
Product Literature Order No	987650-8053
Product Name	Super-Safeway™
Type	Hand Lamps
UPC	78678861264
Woodhead	Yes

**Physical**

Cord Length - Primary	15.24m (50.0')
Cord Length - Secondary	N/A
Depth	58.40mm (2.300")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	N/A
Length	882.65mm (34.750")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

**Electrical**

Bulb Type	Fluorescent
Cord Type - Primary	18/3 SJTW
Lamp Type	F30/T8
Lamp Wattage - Maximum	30W
Lumens	2000
On/Off Switch	Yes
Voltage (Fixture) - Maximum	120VAC 60 HZ

**Material Info**

Old Part Number 1015-3



**EU RoHS**

**Not RoHS Compliant**  
**REACH SVHC**  
 Not Reviewed  
**Low-Halogen Status**  
 Not Reviewed

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[130108Series](#)