

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [10-11-2023](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: [KK® 254 Crimp Housing, High Pressure, 2 Circuits](#)

Documents:

[3D Model](#) [Packaging Specification PK-7880-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-7879 \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family [Crimp Housings](#)
 Series [7880](#)
 Application [Signal, Wire-to-Board](#)
 Overview [KK® Interconnect System - Molex](#)
 Product Name [KK® 254](#)
 UPC [800753612273](#)

Physical


Circuits (maximum) 2
 Color - Resin [Natural \(White\)](#)
 Flammability [94V-0](#)
 Gender [Female](#)
 Glow-Wire Compliant [No](#)
 Material - Resin [Nylon](#)
 Net Weight [0.196/g](#)
 Number of Rows [1](#)
 Packaging Type [Bag](#)
 Panel Mount [No](#)
 Pitch - Mating Interface [2.54mm](#)
 Pitch - Termination Interface [2.54mm](#)
 Stackable [No](#)
 Temperature Range - Operating [See Product Specification](#)

Material Info

Old Part Number [7880-2B](#)

Reference - Drawing Numbers

[Packaging Specification](#) [PK-7880-001](#)
[Product Specification](#) [PS-7879](#)
[Sales Drawing](#) [SD-7880](#)



EU RoHS

**ELV and RoHS
 Compliant**
**REACH SVHC
 Contains SVHC: No**
**Low-Halogen Status
 Low-Halogen**

China RoHS



**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

[7880Series](#)

Mates With

[KK®254 PCB Headers 42375](#) , [42377](#) ,
[42376](#) , [4030](#) , [6373](#) , [6410](#)

Use With

[7879](#) [KK® High Pressure Crimp Terminal](#)