

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [18-12-2602](#)
Status: **Active**
Description: 3.18mm Diameter HCS-125 Pin and Socket Crimp Terminal, Series 1900, Male, with Tin (Sn) Plated Brass Contact, 10-14 AWG, Bag

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PSX-42179 \(PDF\)](#)

Agency Certification

CSA LR19980

General

Product Family Crimp Terminals
 Series [1900](#)
 Application Power
 Crimp Quality Equipment Yes
 MolexKits Yes
 Packaging Alternative [18-12-2601 \(Reel\)](#)
 Product Name HCS-125
 UPC 800754202916

Physical

Gender Male
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 1.223/g
 Packaging Type Bag
 Plating min - Mating 0.508µm
 Plating min - Termination 0.508µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 4.57mm max.
 Wire Size AWG 10, 12, 14
 Wire Size mm² N/A

Material Info

Old Part Number 19001P901L

Reference - Drawing Numbers

Product Specification PSX-42179
 Sales Drawing SD-1900-1*




image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

1900Series

Mates With

1901 Series

Use With

42179 Plug

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extractor Tool for .093 and HCS-125 Product Series	0638240200
Hand Crimper	0638111100

This document was generated on 01/19/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION