

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [43031-0006](#)  
**Status:** **Active**  
**Overview:** Micro-Fit 3.0™ Connectors  
**Description:** Micro-Fit 3.0™ Crimp Terminal, Male, with Select Gold (Au) Plated Tin/Brass Alloy Contact, 26-30 AWG, Reel

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-43045 \(PDF\)](#) [Product Literature \(PDF\)](#)  
[Test Summary TS-43045-002 \(PDF\)](#)

**General**

|                             |   |
|-----------------------------|---|
| Product Family              | Crimp Terminals                           |
| Series                      | <a href="#">43031</a>                     |
| Application                 | Power                                     |
| Crimp Quality Equipment     | Yes                                       |
| Overview                    | <a href="#">Micro-Fit 3.0™ Connectors</a> |
| Packaging Alternative       | <a href="#">43031-0012 (Loose)</a>        |
| Product Literature Order No | 987650-5984                               |
| Product Name                | Micro-Fit 3.0™                            |
| UPC                         | 800754369503                              |

**Physical**

|                                |                      |
|--------------------------------|----------------------|
| Gender                         | Male                 |
| Material - Metal               | Phosphor Bronze      |
| Material - Plating Mating      | Gold                 |
| Material - Plating Termination | Tin                  |
| Net Weight                     | 0.048/g              |
| Packaging Type                 | Reel                 |
| Plating min - Mating           | 0.762µm              |
| Plating min - Termination      | 2.540µm              |
| Termination Interface: Style   | Crimp or Compression |
| Wire Insulation Diameter       | 1.27mm max.          |
| Wire Size AWG                  | 26, 28, 30           |
| Wire Size mm²                  | N/A                  |

**Material Info**

**Reference - Drawing Numbers**

|                       |  |
|-----------------------|--|
| Product Specification | PS-43045, RPS-43045-003, RPS-43045-004 |
| Sales Drawing         | SD-43031-****                          |
| Test Summary          | TS-43045-002                           |




image - Reference only

**EU RoHS**

**ELV and RoHS Compliant**  
**REACH SVHC Contains SVHC: No**  
**Low-Halogen Status Low-Halogen**

**China RoHS**



**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[43031Series](#)

**Mates With**

[43030 Micro-Fit 3.0™ Female Crimp Terminals](#)

**Use With**

[43020](#) , [43640 Micro-Fit 3.0™ Plug Housings](#), [44300 Micro-Fit BMI™ Panel Mount Plug Housings](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

| Description                              | Product #                  |
|--|----------------------------|
| FineAdjust™ Applicator for Insulation OD | <a href="#">0639001600</a> |

|  |   |
|--|---|
| 0.63-1.10mm, 26-30<br>AWG<br>FineAdjust™<br>Applicator for<br>Insulation OD<br>1.12-1.27mm, 26-30<br>AWG Wire<br>T2 Terminator™<br>for insulation OD<br>1.12-1.27mm - 26-30<br>AWG<br>Hand Crimp Tool<br>Extraction Tool<br>Insertion Tool for<br>Crimp Terminal | <br><br><u>0639004400</u><br><br><br><br><u>0639104400</u><br><br><br><br><u>0638190000</u><br><u>0011030043</u><br><u>0638120800</u> |
|--|---|

This document was generated on 02/12/2015

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**