



Machine Tool **LED** Task Light Domed w/ 36" Flexible Arm

Provides illumination over a large surface area

Our domed machine tool task light is ideal for lathes, grinders, presses, assembly, inspection, and many other uses in the shop. The LED element offer significant increase in intensity over that of a standard halogen bulb, while using close to 70% less energy. The head also stays cool to touch and the LEDs have a minimum of 20,000 hours of high-output life. The 36" (898mm) flexible arm holds firmly for precise positioning. It also has a permanent steel bracket for horizontal or vertical mounting. Comes with an 5 foot (152cm) power cord.

Features

- Domed metal shade with black finish
- 36 high intensity energy saving LEDs
- Cool operating temperature
- Exceptionally long LED element life (minimum 20,000 hours)
- Flexible arm for precise positioning
- Provides illumination over a large surface area

MACHINE TOOL LED TASK LIGHT DOMED W/ 36" FLEXIBLE ARM

LED COLOR	36 high intensity white SMD LEDs
LIGHTING CONTROL	On/Off
LED COLOR TEMPERATURE	4000K
LED LIFE	Minimum 20,000 hours
LED OUTPUT	7.7W
OUTPUT VOLTAGE	12V
INPUT VOLTAGE	100-240V
LENGTH OF GOOSENECK	36" (898mm)
DIAMETER OF LAMPSHADE	6.6" (167mm)
ADAPTER	24V, 0.5A
WEIGHT	3lbs (.4kg)
PACKAGE CONTENTS	Machine Tool LED Task Light with Power Adapter

Part #	Description	Price
26532-LED	Machine Tool LED Task Light Domed with 36" Flexible Arm	\$99.00