

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [25001-0406](#)
Status: **Active**
Overview: Ribbon Cable Jumpers
Description: 2.54mm Pitch Board-to-Board Ribbon Cable Jumper - 26 AWG, Stranded Topcoat, 4 Circuits, Strip and Retain, 0.152m Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

| | |
|-------------------------|--------------------------------------|
| Product Family | Cable |
| Series | 25001 |
| Crimp Quality Equipment | Yes |
| Geographic Area | Asia |
| Overview | Ribbon Cable Jumpers |
| Product Name | Ribbon |
| UPC | 800754968423 |

Physical

| | |
|-------------------------------|--------------------------|
| Cable Length | 0.152m |
| Circuits (Loaded) | 4 |
| Circuits (maximum) | 4 |
| Insulation | PVC |
| Net Weight | 1.941/g |
| Packaging Type | Bag |
| Pitch - Termination Interface | 2.54mm |
| Temperature Range - Operating | -20°C to +105°C |
| Wire Size AWG | 26 |
| Wire/Cable Type | (7x34) Stranded, Topcoat |

Electrical

| | |
|-------------------------------|------|
| Current - Maximum per Contact | N/A |
| Voltage - Maximum | 300V |

Material Info

Reference - Drawing Numbers

| | |
|---------------|--------------|
| Sales Drawing | SD-25001-001 |
|---------------|--------------|



image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Not Reviewed**
**Low-Halogen Status
Not Reviewed**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[25001Series](#)