

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [06-66-0012](#)
Status: **Active**
Overview: [Pre-Crimped Leads](#)
Description: Pre-Crimped Lead PicoBlade™ Female-to-PicoBlade™ Female, 152mm, 28 AWG

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	666
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	PicoBlade™ Crimp Terminals
Overview	Pre-Crimped Leads
Product Name	PicoBlade™
UPC	800754232906

Physical

Cable Length	0.15m
Circuits (Loaded)	1
Color - Resin	Red
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	25.430/g
Packaging Type	Bag
Single Ended	No
Wire Size AWG	28
Wire/Cable Type	Discrete Wire

Material Info

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

**Contains SVHC: No
Low-Halogen Status
Not Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
 non-product compliance questions.

Search Parts in this Series

666Series

Mates With

[50125](#) Crimp Terminal, [50133](#) Crimp
 Terminal

Use With

PicoBlade™ Housings [51021](#)