

Snap Action, Subminiature


Features

- Actuator: Hinge Roller Lever



NTE Type No.	Circuitry	Max. Free Position	Min. Over Travel	Max. Operating Force	Max. Differential	Diag No.
54-416	SPDT	0.693"	0.032"	55g	0.032"	S45

S45



Specifications

Current Rating: 10A 125VAC
Contact Resistance: 30 Milliohms (max.) initial
Insulation Resistance: 100 Megohms at 500VDC
Dielectric Strength: 1000VAC (50/60Hz for 1 minute)
Temperature Rating: -13° to +185°F (-25° to +85°C)
Electrical Life: 50,000 cycles min.
Mechanical Life: 1,000,000 cycles min.
Terminal Type: Solder Terminals

Snap Action, Subminiature


Features

- Actuator: Hinge Lever



NTE Type No.	Circuitry	Max. Free Position	Min. Over Travel	Max. Operating Force	Max. Differential	Diag No.
54-417	SPDT	0.469"	0.039"	55g	0.032"	S46

S46



Specifications

Current Rating: 10A 125VAC
Contact Resistance: 30 Milliohms (max.) initial
Insulation Resistance: 100 Megohms at 500VDC
Dielectric Strength: 1000VAC (50/60Hz for 1 minute)
Temperature Rating: -13° to +185°F (-25° to +85°C)
Electrical Life: 50,000 cycles min.
Mechanical Life: 1,000,000 cycles min.
Terminal Type: Solder Terminals