

**Specifications:**

Resonant Frequency (Hz)	400 ± 100
Operating Voltage (Vdc)	4 ~ 8
Rated Voltage (Vdc)	6
Current Consumption Max. (mA)	30 at Rated Voltage
Sound Pressure Level Min. (dB)	80 at 30cm at Rated Voltage
Tone/Pulse Rate	Constant
Operating Temperature (°C)	-20 ~ +70
Storage Temperature (°C)	-30 ~ +85
Housing	ABS 757 plastic resin (Color: Black)
Leading Pin	Tin Plated Brass
Condition by Hand Soldering (°C)	350 ± 20° within 5 seconds
Weight (Grams)	8.8
Options	For other options contact factory

**Dimensions:** (units: mm)**ROHS Compliant**