


Part Number: 19211003

Type	Size	Rating	Description
LED	M14	2.0VDC	Standard Bezel Panel Indicator



Part #	Colour	Voltage(V)	DC Current(mA)	Intensity(mcd)
19211003	Red	2.0VDC	30max.	200 @ 20mA

Notes:

- 1 Black Chrome Bezel
- 2 Electrical & optical data are measured at an ambient temperature of 25°C
- 3 Luminous intensity at DC
- 4 Storage temperature -25 °C to +80°C
- 5 Application temperature -20 °C to +60°C
- 6 Voltage tolerance ±10%
- 7 Due to component tolerances, colour temperature variations may be observed
- 8 Degree of protection IP67 when used with the supplied gasket
- 9 The plastic(polycarbonate) has limited chemical resistance
- 10 RoHS & REACH SVHC compliant