

HEAVY DUTY ENCLOSURES

91 Series IP67 Low Profile Cases

Beautifully designed low profile IP67 waterproof enclosures, ideal for tracking/monitoring in harsh environments.

- IP67 rated, perfect for outdoor applications
- White enclosures made from ASA UL94-HB plastic for high ultraviolet resistance
- Dark Grey enclosures made from ABS UL94-V0 plastic for high flammability rating
- Wall mount holes behind hinged caps for superior aesthetic finish
- Mount Kit accessory for easy mounting to poles, pillars, posts and lamp posts

SPECIFICATION

Material:

Dark grey Lid & base ABS UL94-V0


White grey Lid & base ASA UL94-HB

Operating Temperature -10°C to +60°C

Standard colours Dark grey or white grey

Standard unit includes Lid, base, gasket & fixing screws

TAKACHI



DARK GREY	WHITE GREY	LENGTH	WIDTH	HEIGHT
CHD91E1DG	CHD91E1WG	130	90	25
CHD91E2DG	CHD91E2WG	130	90	40
CHD91E3DG	CHD91E3WG	100	100	25
CHD91E4DG	CHD91E4WG	100	100	40
CHD91E5DG	CHD91E5WG	150	110	27
CHD91E6DG	CHD91E6WG	150	110	40



Pole Mount Kit

PART NO.	LENGTH	WIDTH	HEIGHT	DESCRIPTION
CHD91PMDG	28	18	12	POLE MOUNT KIT, DARK GREY
CHD91PMWG	28	18	12	POLE MOUNT KIT, WHITE GREY



Rubber Feet

PART NO.	LENGTH	WIDTH	HEIGHT
CHD91FEET	10	10	7.5