


## Coaxial Cable Connector 16\_MM CX-50-2-4/111\_O

### Description

Right angle cable plug

Interface standards  
SUHNER-MM CX



### Technical Data

#### Electrical Data

Impedance 50  $\Omega$   
Interface frequency max. 6 GHz

#### Mechanical Data

Centre contact soldered  
Outer 2contact crimped  
Weight 0.0009 kg

#### Environmental Data

Operating temperature -55 °C to 155 °C  
2011/65/EU (RoHS) compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Gold Plating (without Nickel underplating)
Body	Brass	Gold Plating (without Nickel underplating)
Insulator	PFA / PTFE	
Crimp ferrule	Copper	

### Related Documents

Outline drawing DOU-00006003  
Catalogue drawing DOU-00006005  
Assembly instruction DOC-0000241539

### Ordering Information

Bulk 100 pcs package 16\_MM CX-50-2-4/111\_OH  
Single package 16\_MM CX-50-2-4/111\_OE

### Additional Information

Suitable cables RG\_316\_/U, ENVIROFLEX\_316, RG\_188\_A/U, RG 174 /U