



LOGO! 24RCE, LOGICMODULE, DISPLAY PU/I/O: 24V AC/24V DC/RELAY, 8 DI/4 DO; MEM. 400 BLOCKS, EXPANDABLE, ETHERNET BUILT IN WEB-SERVER, DATALOG STANDARD MICRO SD CARD FOR LOGO! SOFT COMFORT V8 PREVIOUS PROJECT USABEL

Installation type/mounting

Mounting	on 35 mm DIN rail, 4 spacing units wide
----------	---

Supply voltage

24 V DC	Yes
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
24 V AC	Yes

Time of day

Time switching clocks

- | | |
|-----------------|-------|
| • Number | 8 |
| • Power reserve | 480 h |

Digital inputs

Number of digital inputs	8
--------------------------	---

Digital outputs

Number of digital outputs	4; Relays
Short-circuit protection	No; external fusing necessary

Relay outputs

Switching capacity of contacts	
— with inductive load, max.	3 A
— with resistive load, max.	10 A

EMC

Emission of radio interference acc. to EN 55 011

- | | |
|--|-----|
| • Emission of radio interference acc. to EN 55 011 (limit class B) | Yes |
|--|-----|

Degree and class of protection

IP20	Yes
------	-----

Standards, approvals, certificates

CSA approval	Yes
UL approval	Yes
FM approval	Yes
developed in accordance with IEC 61131	Yes
acc. to VDE 0631	Yes

Marine approval

• Marine approval	Yes
-------------------	-----

Ambient conditions

Operating temperature

• min.	0 °C
• max.	55 °C

Dimensions

Width	71.5 mm
Height	90 mm
Depth	60 mm
last modified:	21.08.2014