


ATM Equivalent – Low Voltage Miniature Automotive, Fast Acting

Features

- Miniature Blade Type
- RoHS Compliant



F-05



Specifications

Rated Voltage: 32V

Time Current Characteristics:


| % of Ampere Rating | Opening Time |
|--------------------|---------------------|
| 110% | 4 hours min. |
| 135% | 0.75 – 1800 seconds |
| 200% | 0.15 – 5 seconds |
| 300% | 0.08 seconds max. |

| NTE Type No. | Rated Current | Color Code | Diag No. |
|--------------|---------------|------------|----------|
| NEW 74-MAF2A | 2A | Gray | F-05 |
| NEW 74-MAF3A | 3A | Violet | F-05 |
| NEW 74-MAF4A | 4A | Pink | F-05 |
| 74-MAF5A | 5A | Tan | F-05 |
| 74-MAF7.5A | 7.5A | Brown | F-05 |
| 74-MAF10A | 10A | Red | F-05 |
| 74-MAF15A | 15A | Blue | F-05 |
| 74-MAF20A | 20A | Yellow | F-05 |
| 74-MAF25A | 25A | Natural | F-05 |
| 74-MAF30A | 30A | Green | F-05 |


ATC Equivalent - Low Voltage Automotive, Fast Acting

Features

- Fast Acting
- RoHS Compliant



F-06



Specifications

Rated Voltage: 32V

Time Current Characteristics:

| % of Ampere Rating | Opening Time |
|--------------------|-------------------|
| 110% | 100 hours min. |
| 135% | 1800 seconds max. |
| 200% | 5 seconds max. |
| 300% | 0.08 seconds max. |

| NTE Type No. | Rated Current | Color Code | Diag No. |
|--------------|---------------|------------|----------|
| NEW 74-AF1A | 1A | Black | F-06 |
| NEW 74-AF2A | 2A | Gray | F-06 |
| NEW 74-AF3A | 3A | Violet | F-06 |
| NEW 74-AF4A | 4A | Pink | F-06 |
| 74-AF5A | 5A | Tan | F-06 |
| 74-AF7.5A | 7.5A | Brown | F-06 |
| 74-AF10A | 10A | Red | F-06 |
| 74-AF15A | 15A | Blue | F-06 |
| 74-AF20A | 20A | Yellow | F-06 |
| 74-AF25A | 25A | Natural | F-06 |
| 74-AF30A | 30A | Green | F-06 |