

MPX-410DMP - Stereo Mixer



Stereo DJ mixer with integrated MP3 player and Bluetooth receiver

Mixer:

- 4 stereo input channels, switchable MP3/phono/line (channel 1), aux/phono/line (channel 2) and aux/mic/line (channels 3-4)
- Input channels, each with gain control and 2-way tone control
- 1 DJ microphone channel, adjustable, with 2-way tone control
- Adjustable headphone output with pre-fader listening (PFL) to the stereo input channels and the master output
- Crossfader with assignment switches
- Master output with stereo LED level display
- Additional outputs booth and record

MP3 player with Bluetooth receiver, USB interface and SD/MMC card slot:

- Bluetooth receiver for the wireless connection of laptops, smartphones or tablet PCs
- USB storage media can be connected directly (e.g. USB flash drive)



- For SD/MMC cards up to 32 GB (FAT 6/FAT 32), available at option
- Alphanumeric display
- Repeat function
- Blue backlit display

Technical data

Mic input	: 1.5 mV
Phono input	: 2 mV (phono 1-2)
CD input	: -
Line input	: 200 mV (line 1-4) 200 mV (aux 1-3)
Master output	: 1 V (XLR, bal.)
Record output	: 400 mV (tape) 1 V (booth)
Headphones	: ≥ 8 Ohm, stereo
Frequency range	: 20-20,000 Hz
THD	: < 0.15 %
S/N ratio	: ? 60 dB, unweighted
Equalizer, bass	: ±15 dB/50 Hz (ch. 1-4) ±12 dB/100 Hz (DJ mic)
Equalizer, midrange	: -
Equalizer, treble	: ±15 dB/10 kHz (ch. 1-4) ±12 dB/7 kHz (DJ mic)
Talkover	: -
Gooseneck light	: -
Power supply	: 230 V~/50 Hz/15 VA
Admiss. ambient temp.	: 0-40 °C
Dimensions	: 482x88x105 mm, 2 RS
Weight	: 2.2 kg