

DYNAMO85


850VA Compact UPS with 4 IEC Outputs

Total Electrical Backup Power for Digital Lifestyle.

The new **DYNAMO85** is a high-specification Uninterruptible Power Supply (UPS) for IT, Telco, Networking and Broadcast level digital equipment.

Featuring a new and improved full 850VA sealed, maintenance free Battery, the UPS can deliver sustained electrical power output up to around 1 hour *. Built-in 4-Port female IEC connectors allow a mixed environment of devices to be connected including Servers, Workstations, Routers and Networking devices. Ideal also for Telco and PABX equipment, the **DYNAMO85** conditions the input power to remove common electrical problems including Power Spikes, Noise and Brownouts that cause data corruption and reduce equipment lifespan.

Compact, stylish and complete with visual and audible warnings, the new **DYNAMO85** features total maintenance free operation. Totally silent in operation together with user replaceable fuses to further reduce expensive downtime for your equipment.



Ideal for Computer, Networking, Telco and Broadcast Protection!

Advanced features...

Maximum Capacity ~ **850VA/600W**

Battery Type ~ **Sealed, maintenance free lead acid**

Typical Protection ~ **10 – 60 Minutes under nominal load***

Inversion ~ **Simulated 'Sine Wave' type**

Transfer Time ~ **10ms (including detection time)**

Battery Protection ~ **Auto self-test, discharge protection**

Input Voltage ~ **230 Volts (+20%, -25%), 50Hz (+/- 20%)**

Output Voltage ~ **230 Volts AC (+/- 10%), 50-120Hz**

Recharge Time ~ **6-8 Hours to 90% full capacity**

Power Output Interfaces ~ **4 female IEC type connectors**

Visual Indicators ~ **3 LED for 'online', 'offline', 'low charge'**

Audible Indicators ~ **Buzzer sound for battery switch over**

**Actual Battery Backup Times may vary, depending on load*

 **Dynamode**

For the complete range visit www.DYNAMODE.com

© 2011 Dynamode
Details correct at going to press. E&OE
All Trademarks Acknowledged