

TEMPO TA201610T



Order symbol: TA201610T
Product nbr: 5814006
Description: Enclosure, ABS
Remarks: Clear transparent cover

EAN: 6418074060785
EI. number:
 Finland: 3435694
 Electric No. Denmark: 8212035030
 Electric No. Sweden: 5814006

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	201	163	98	DH-3 DIN-35 Mounting rail
inch:	7.9	6.4	3.9	ARH 2320 DIN-35 Mounting rail
Materials:				FP 10674
Material:	ABS			DPS 14553 Grey sealing plug set
Base colour:	RAL 7035 -light grey			Rating:
Cover screws material:	Polyamide			Ingress Protection (EN 60529): IP65
Cover colour:	Clear transparent			Impact Resistance (EN 62262): IK07
Cover screws colour:	Grey			Electrical insulation: Totally insulated
Gasket material:	Polyurethane			Halogen free (DIN/VDE 0472, Part 815): 1
Temperatures:				Flammability Rating: UL 94 HB
Temperature °C (short term):	-40 ... 80 °C			Glow Wire Test (IEC 695-2-1) °C: 650
Temperature °C (continuous):	-40 ... 60 °C			Certificates:
Temperature °F (short term):	-40 ... 175 °F			SGS Fimko
Temperature °F (continuous):	-40 ... 140 °F			
Accessories:				
MP 2016	Mounting plate			

TEMPO 201x163x98

