

TEMPO TA241911T



Order symbol: TA241911T
Product nbr: 5814007
Description: Enclosure, ABS
Remarks: Clear transparent cover

EAN: 6418074060792
EI. number:
 Finland: 3435696
 Electric No. Denmark: 8212035056
 Electric No. Sweden: 5814007

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Sample photo

| Dimensions: | Length | Width | Height | Accessories: |
|-------------|--------|-------|--------|--------------------------------|
| mm: | 240 | 191 | 107 | EKV 12 DIN-35 Mounting rail |
| inch: | 9.4 | 7.5 | 4.2 | DR 210 DIN-35 Mounting rail |
| | | | | FP 10674 |

| Materials: | Material | Rating: |
|-------------------------------|----------------------|--|
| Material: | ABS | Ingress Protection (EN 60529): IP65 |
| Base colour: | RAL 7035 -light grey | Impact Resistance (EN 62262): IK07 |
| Cover screws material: | Polyamide | Electrical insulation: Totally insulated |
| Cover colour: | Clear transparent | Halogen free (DIN/VDE 0472, Part 815): 1 |
| Cover screws colour: | Grey | Flammability Rating: UL 94 HB |
| Gasket material: | Polyurethane | Glow Wire Test (IEC 695-2-1) °C: 650 |

| Temperatures: | Certificates: |
|--|---------------|
| Temperature °C (short term): -40 ... 80 °C | SGS Fimko |
| Temperature °C (continuous): -40 ... 60 °C | |
| Temperature °F (short term): -40 ... 175 °F | |
| Temperature °F (continuous): -40 ... 140 °F | |

| Accessories: |
|---|
| MP 2419 Mounting plate |

