



Order symbol: TAM111107
Product nbr: 5814021
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074011435
EI. number:
 Finland: 3438264
 Electric No. Denmark: 8212045266
 Electric No. Sweden: 5814021

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions:				Accessories:	
	Length	Width	Height		
mm:	110	110	65	DRM 80	DIN-15 Mounting rail
inch:	4.3	4.3	2.6	FP 10674	
				DPS 14553	Grey sealing plug set
Materials:				Rating:	
Material:	ABS			Ingress Protection (EN 60529): IP65	
Base colour:	RAL 7035 -light grey			Impact Resistance (EN 62262): IK07	
Cover screws material:	Polyamide			Electrical insulation: Totally insulated	
Cover colour:	RAL 7035 -light grey			Halogen free (DIN/VDE 0472, Part 815): 1	
Cover screws colour:	Grey			Flammability Rating: UL 94 HB	
Gasket material:	Polyurethane			Glow Wire Test (IEC 695-2-1) °C: 650	
Temperatures:				Certificates:	
Temperature °C (short term):	-40 ... 80 °C			SGS Fimko	
Temperature °C (continuous):	-40 ... 60 °C				
Temperature °F (short term):	-40 ... 175 °F				
Temperature °F (continuous):	-40 ... 140 °F				
Accessories:					
MP 1111	Mounting plate				

