



Order symbol: TAM131007
Product nbr: 5814022
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074011442
EI. number:
 Finland: 3438265
 Electric No. Denmark: 8212045279
 Electric No. Sweden: 5814022

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions:	Length	Width	Height	Accessories:
mm:	130	95	65	MP 1310 Mounting plate
inch:	5.1	3.7	2.6	FP 10674 DPS 14553 Grey sealing plug set

Materials:	Rating:
Material: ABS	Ingress Protection (EN 60529): IP65
Base colour: RAL 7035 -light grey	Impact Resistance (EN 62262): IK07
Cover screws material: Polyamide	Electrical insulation: Totally insulated
Cover colour: RAL 7035 -light grey	Halogen free (DIN/VDE 0472, Part 815): 1
Cover screws colour: Grey	Flammability Rating: UL 94 HB
Gasket material: Polyurethane	Glow Wire Test (IEC 695-2-1) °C: 650

Temperatures:	Certificates:
Temperature °C (short term): -40 ... 80 °C	SGS Fimko
Temperature °C (continuous): -40 ... 60 °C	
Temperature °F (short term): -40 ... 175 °F	
Temperature °F (continuous): -40 ... 140 °F	

Accessories:
DRM 100 DIN-15 Mounting rail

