

TEMPO TAM131308



Order symbol: TAM131308
Product nbr: 5814023
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074011459
EI. number:
 Finland: 3438266
 Electric No. Denmark: 8212045282
 Electric No. Sweden: 5814023

Including: Base with PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Sample photo

Dimensions: Length Width Height Accessories:

mm:	130	130	75	MIV 10	DIN-35 Mounting rail
inch:	5.1	5.1	3.0	MP 1313	Mounting plate
				FP 10674	

Materials: DPS 14553 Grey sealing plug set

Material: ABS	Rating:
Base colour: RAL 7035 -light grey	Ingress Protection (EN 60529): IP65
Cover screws material: Polyamide	Impact Resistance (EN 62262): IK07
Cover colour: RAL 7035 -light grey	Electrical insulation: Totally insulated
Cover screws colour: Grey	Halogen free (DIN/VDE 0472, Part 815): 1
Gasket material: Polyurethane	Flammability Rating: UL 94 HB
	Glow Wire Test (IEC 695-2-1) °C: 650

Temperatures: Certificates:

Temperature °C (short term): -40 ... 80 °C	Certificates: SGS Fimko
Temperature °C (continuous): -40 ... 60 °C	
Temperature °F (short term): -40 ... 175 °F	
Temperature °F (continuous): -40 ... 140 °F	

Accessories:

DRM 100	DIN-15 Mounting rail
---------	----------------------

