

TEMPO TAM191209



Order symbol: TAM191209
Product nbr: 5814024
Description: Enclosure, ABS
Remarks: Grey cover

EAN: 6418074062666
EI. number:
Finland: 3438005
Electric No. Sweden: 5814024

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Sample photo

Dimensions:		Length	Width	Height	Accessories:	
mm:		187	122	90	MIV 10	DIN-35 Mounting rail
inch:		7.4	4.8	3.5	DH-3	DIN-35 Mounting rail
Materials:					FP 10674	
Material:	ABS				DPS 14553	Grey sealing plug set
Base colour:	RAL 7035 -light grey				Rating:	
Cover screws material:	Polyamide				Ingress Protection (EN 60529): IP65	
Cover colour:	RAL 7035 -light grey				Impact Resistance (EN 62262): IK07	
Cover screws colour:	Grey				Electrical insulation: Totally insulated	
Gasket material:	Polyurethane				Halogen free (DIN/VDE 0472, Part 815): 1	
Temperatures:					Flammability Rating: UL 94 HB	
Temperature °C (short term):	-40 ... 80 °C				Glow Wire Test (IEC 695-2-1) °C: 650	
Temperature °C (continuous):	-40 ... 60 °C				Certificates:	
Temperature °F (short term):	-40 ... 175 °F				SGS Fimko	
Temperature °F (continuous):	-40 ... 140 °F					
Accessories:						
MP 1912	Mounting plate					

