

MNX PCM 200/63 G



Sample photo

Order symbol: PCM 200/63 G
Product nbr: 6016324
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074051950
EI. number:
 Finland: 3435270
 Electric No. 8212027446
 Denmark:
 Electric No. Sweden: 2535342

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Accessories:		
Length	Width	Height			
mm:	255	180	63	MIN 15	DIN-15 Mounting rail
inch:	10.0	7.1	2.5	MIN 20	DIN-15 Mounting rail
Materials:			MIV 15	DIN-35 Mounting rail	
Material:	Polycarbonate		MIV 20	DIN-35 Mounting rail	
Base colour:	RAL 7035 -light grey		FP A 200/180	Front plate (Aluminium)	
Cover screws material:	Polyamide		HFP 180	Front plate hinge series	
Cover colour:	RAL 7035 -light grey		FP 22046	Wall fastening lug (4 pcs)	
Cover screws colour:	Grey		Rating:		
Gasket material:	TPE		Ingress Protection (EN 60529): IP66/67		
Temperatures:			Impact Resistance (EN 62262): IK08		
Temperature °C (short term):	-40 ... 120 °C		Electrical insulation: Totally insulated		
Temperature °C (continuous):	-40 ... 80 °C		Halogen free (DIN/VDE 0472, Part 815): 1		
Temperature °F (short term):	-40 ... 250 °F		UV resistance: UL 508		
Temperature °F (continuous):	-40 ... 175 °F		Flammability Rating: UL 746C 5V		
Accessories:			Glow Wire Test (IEC 695-2-1) °C: 960		
MIV 200	Mounting plate (Galvanized steel)		NEMA Class: NEMA 1, 4, 4X, 6, 12, 13		
			Certificates:		
			Germanischer Lloyd (GL)		
			SGS Fimko		
			Gost R		

