

MNX PC 100/100 HG



Sample photo

Order symbol: PC 100/100 HG
Product nbr: 6011303
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074022059
EI. number:
 Finland: 3420313
 Electric No. 8212022043
 Denmark:
 Electric No. Italy: 7351030
 Electric No. Sweden: 2535515

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

| Dimensions: | | | | Accessories: | |
|-------------------------------------|-----------------------------------|-------|--------|--|----------------------------|
| | Length | Width | Height | | |
| mm: | 130 | 80 | 100 | MIN 5 | DIN-15 Mounting rail |
| inch: | 5.1 | 3.1 | 3.9 | MIN 10 | DIN-15 Mounting rail |
| Materials: | | | | MIV 5 | DIN-35 Mounting rail |
| Material: | Polycarbonate | | | MIV 10 | DIN-35 Mounting rail |
| Base colour: | RAL 7035 -light grey | | | FP A 100/130 | Front plate (Aluminium) |
| Cover screws material: | Polyamide | | | HFP 130 | Front plate hinge series |
| Cover colour: | RAL 7035 -light grey | | | FP 22046 | Wall fastening lug (4 pcs) |
| Cover screws colour: | Grey | | | Rating: | |
| Gasket material: | TPE | | | Ingress Protection (EN 60529): IP66/67 | |
| Temperatures: | | | | Impact Resistance (EN 62262): IK08 | |
| Temperature °C (short term): | -40 ... 120 °C | | | Electrical insulation: Totally insulated | |
| Temperature °C (continuous): | -40 ... 80 °C | | | Halogen free (DIN/VDE 0472, Part 815): 1 | |
| Temperature °F (short term): | -40 ... 250 °F | | | UV resistance: UL 508 | |
| Temperature °F (continuous): | -40 ... 175 °F | | | Flammability Rating: UL 746C 5V | |
| Accessories: | | | | Glow Wire Test (IEC 695-2-1) °C: 960 | |
| MIV 100 | Mounting plate (Galvanized steel) | | | NEMA Class: NEMA 1, 4, 4X, 6 | |
| | | | | Certificates: | |
| | | | | Germanischer Lloyd (GL) | |
| | | | | SGS Fimko | |
| | | | | Gost R | |

