


MNX PC 125/60 HT



Sample photo

Order symbol: PC 125/60 HT
Product nbr: 6011907
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074022349
EI. number:
 Finland: 3420441
 Electric No. Denmark: 8212022399
 Electric No. Italy: 7352055
 Electric No. Sweden: 2535630

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Accessories:		
mm:		130	130	60	MIN 10	DIN-15 Mounting rail	
inch:		5.1	5.1	2.4	MIV 10	DIN-35 Mounting rail	
Materials:						FP A 125/130	Front plate (Aluminium)
Material:		Polycarbonate				HFP 130	Front plate hinge series
Base colour:		RAL 7035 -light grey				FP 22046	Wall fastening lug (4 pcs)
Cover screws material:		Polyamide				Rating:	
Cover colour:		Smoked grey				Ingress Protection (EN 60529): IP66/67	
Cover screws colour:		Black				Impact Resistance (EN 62262): IK08	
Gasket material:		TPE				Electrical insulation: Totally insulated	
Temperatures:						Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °C (short term):		-40 ... 120 °C				UV resistance: UL 508	
Temperature °C (continuous):		-40 ... 80 °C				Flammability Rating: UL 746C 5V	
Temperature °F (short term):		-40 ... 250 °F				Glow Wire Test (IEC 695-2-1) °C: 960	
Temperature °F (continuous):		-40 ... 175 °F				NEMA Class: NEMA 1, 4, 4X, 6	
Accessories:						Certificates:	
MIV 125		Mounting plate (Galvanized steel)				Germanischer Lloyd (GL)	
						SGS Fimko	
						Gost R	

