

MNX PC 125/125 HT



Sample photo

Order symbol: PC 125/125 HT
Product nbr: 6011910
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074022363
EI. number:
 Finland: 3420445
 Electric No. Denmark: 8212022412
 Electric No. Italy: 7352065
 Electric No. Sweden: 2535636

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Accessories:		
mm:		130	130	125	MIN 10	DIN-15 Mounting rail	
inch:		5.1	5.1	4.9	MIV 10	DIN-35 Mounting rail	
Materials:						FP A 125/130	Front plate (Aluminium)
Material:	Polycarbonate					HFP 130	Front plate hinge series
Base colour:	RAL 7035 -light grey					FP 22046	Wall fastening lug (4 pcs)
Cover screws material:	Polyamide					Rating:	
Cover colour:	Smoked grey					Ingress Protection (EN 60529): IP66/67	
Cover screws colour:	Black					Impact Resistance (EN 62262): IK08	
Gasket material:	TPE					Electrical insulation: Totally insulated	
Temperatures:						Halogen free (DIN/VDE 0472, Part 815): 1	
Temperature °C (short term):	-40 ... 120 °C					UV resistance: UL 508	
Temperature °C (continuous):	-40 ... 80 °C					Flammability Rating: UL 746C 5V	
Temperature °F (short term):	-40 ... 250 °F					Glow Wire Test (IEC 695-2-1) °C: 960	
Temperature °F (continuous):	-40 ... 175 °F					NEMA Class: NEMA 1, 4, 4X, 6	
Accessories:						Certificates:	
MIV 125	Mounting plate (Galvanized steel)					Germanischer Lloyd (GL)	
						SGS Fimko	
						Gost R	

