

**MNX PCM 300/150 ZT**



Sample photo

**Order symbol:** PCM 300/150 ZT  
**Product nbr:** 6016938  
**Description:** Enclosure, PC  
**Remarks:** Smoked transparent cover

**EAN:** 6418074061560  
**EI. number:**  
 Finland: 3435674  
 Electric No. 8212027860  
 Denmark:  
 Electric No. Sweden:

Including: Base with metric knock-outs and PUR gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:	Length	Width	Height	Accessories:
mm:	360	255	152	MIV 200 MIV 150 MIN 20 MIN 15 MIV 30 MIV 20 MIV 15 FP 10674
inch:	14.2	10.0	6.0	Mounting plate (Galvanized steel) Mounting plate (Galvanized steel) DIN-15 Mounting rail DIN-15 Mounting rail DIN-35 Mounting rail DIN-35 Mounting rail DIN-35 Mounting rail

**Materials:**

**Material:** Polycarbonate  
**Base colour:** RAL 7035 -light grey  
**Cover screws material:** Polyamide  
**Cover colour:** Smoked grey  
**Cover screws colour:** Black  
**Gasket material:** Polyurethane

**Temperatures:**

**Temperature °C (short term):** -40 ... 120 °C  
**Temperature °C (continuous):** -40 ... 80 °C  
**Temperature °F (short term):** -40 ... 250 °F  
**Temperature °F (continuous):** -40 ... 175 °F

**Accessories:**

MIV 300                      Mounting plate (Galvanized steel)

**Rating:**

Ingress Protection (EN 60529): IP66/67  
 Impact Resistance (EN 62262): IK08  
 Electrical insulation: Totally insulated  
 Halogen free (DIN/VDE 0472, Part 815): 1  
 UV resistance: UL 508  
 Flammability Rating: UL 746C 5V  
 Glow Wire Test (IEC 695-2-1) °C: 960  
 NEMA Class: NEMA 1, 4, 4X, 6, 12, 13

