

**TEMPO TA292411T**



**Order symbol:** TA292411T  
**Product nbr:** 5814008  
**Description:** Enclosure, ABS  
**Remarks:** Clear transparent cover

**EAN:** 6418074060808  
**EI. number:**  
**Finland:** 3435698  
**Electric No. Denmark:** 8212035072  
**Electric No. Sweden:** 5814008

Including: Base with PUR gasket and screws for mounting plate/DIN-rail, cover with polyamide cover screws and plastic hinges.

Sample photo

Dimensions:				Accessories:	
Length	Width	Height			
mm:	289	239	107	DR 215	DIN-35 Mounting rail
inch:	11.4	9.4	4.2	DR 265	DIN-35 Mounting rail
Materials:				FP 10674	
<b>Material:</b>	ABS			DPS 14553	Grey sealing plug set
<b>Base colour:</b>	RAL 7035 -light grey			Rating:	
<b>Cover screws material:</b>	Polyamide			Ingress Protection (EN 60529): IP65	
<b>Cover colour:</b>	Clear transparent			Impact Resistance (EN 62262): IK07	
<b>Cover screws colour:</b>	Grey			Electrical insulation: Totally insulated	
<b>Gasket material:</b>	Polyurethane			Halogen free (DIN/VDE 0472, Part 815): 1	
Temperatures:				Flammability Rating: UL 94 HB	
<b>Temperature °C (short term):</b>	-40 ... 80 °C			Glow Wire Test (IEC 695-2-1) °C: 650	
<b>Temperature °C (continuous):</b>	-40 ... 60 °C			Certificates:	
<b>Temperature °F (short term):</b>	-40 ... 175 °F			SGS Fimko	
<b>Temperature °F (continuous):</b>	-40 ... 140 °F				
Accessories:					
MP 2924	Mounting plate				

