

Protect It! 1-Outlet Surge Protector, Direct Plug-In, 350 Joules, Timer Selection Switch

MODEL NUMBER: SK10TG



Highlights

- 1 outlets/direct plug-in
- 350 joule rating
- Timer selection switch for 1, 3, or 6 hours
- Diagnostic LEDs
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Ideal for any desktop, network or home computing application requiring AC protection

Package Includes

- SK10TG surge suppressor
- Instruction sheet

Description

The SK10TG surge suppressor with timer offers reliable surge and line noise protection. The compact direct plug-in design allows for easy portability and features 1 outlet and 350 joules of surge energy absorption. Timer selection switch for 1, 3, or 6 hours helps make connected devices more energy efficient. On/Off push button lets you shut off outlet at any time. Diagnostic LEDs alert you to potential wiring or protection faults before connected equipment is damaged. \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 1 outlets / direct plug-in
- Surge suppression rating: 350 joules
- Timer Feature
- EMI/RFI noise filtering
- Diagnostic LEDs indicate Protected (green) & Grounded (red)
- \$5,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Specifications

OVERVIEW	
Style	Direct Plug-In
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1875
Circuit Breaker (amps)	15
Outlet Type	NEMA 5-15P



INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V
Input Connection Type	NEMA 5-15P input plug
Input Plug Features	120V, 15A
Input Cord Length (ft.)	0
Input Cord Length Details	Direct Plug-In
Voltage Compatibility (VAC)	120
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	350
AC Suppression Response Time	< 1ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
Clamping Voltage (RMS)	400
AC Suppression Surge Current Rating	27,000
UL1449 Let Through Rating	500, 400, 500
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
PHYSICAL	
Unit Dimensions (hwd / in.)	2.76 x 2.76 x 1.50
Unit Dimensions (hwd / cm)	7 x 7 x 3.8
Unit Weight (lbs.)	.22
Unit Weight (kg)	.10
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Direct plug-in suppressor mounts directly to a wall receptacle
Housing Color	Black
Receptacle Color	Black
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$5,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.