

For Patient-Care Vicinity - UL60601-1 Medical-Grade Power Strip with 4 Hospital-Grade Outlets, 15-ft. Cord, Safety Covers

MODEL NUMBER: PS-415-HGULTRA



Description

Offering AC power distribution for 120V applications in a rugged all-metal case, Tripp Lite's PS-415-HGULTRA is agency approved for use in a variety of healthcare venues, including physicians' offices, imaging centers, laboratories and more. Featuring unique, patented (U.S. No. 7,375,939), it resets automatically with no need for action by the user. Features include switchless design to prevent accidental shutoff, four NEMA 5-15R-HG hospital-grade outlets with safety covers, NEMA 5-15P-HG hospital-grade plug, 15A resettable circuit breaker, and optional-use keyhole mounting slots and flanges.

Features

- Approved for use in Patient Care Areas
- Rugged all-metal housing stands up to the most demanding environments
- 4 x NEMA 5-15R-HG outlets with safety covers
- 15-ft. cord with NEMA 5-15P-HG plug
- Switchless design prevents accidental shutoff
- 15A circuit breaker
- Multiple installation options with integral mounting flanges and slots
- UL 60601-1 and UL 60950-1 compliant
- U.S. Patent No. 7,375,939
- Suitable for use where Article 517 of the NEC requires Hospital-Grade Outlets

Highlights

- Fully tested, certified and compliant with UL 60601-1 and UL 60950-1
- 4 hospital-grade outlets with safety covers
- Switchless design prevents accidental shutoff
- 15-ft. cord with hospital-grade plug
- Rugged all-metal case
- Approved for use within 6-ft. of patient-care areas

Applications

- AC power distribution with hospital-grade receptacles and plug in healthcare applications where durability and reliability are required, including areas where NEC requires hospital-grade receptacles
- Patient rooms, treatment rooms, exam rooms, etc.

Package Includes

- PS-415-HGULTRA Medical-Grade Power Strip
- Owner's manual with warranty information

Specifications

OVERVIEW

Style	Strip
-------	-------



Model Type	For Patient-Care Areas
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	15A resettable circuit breaker
Outlet Safety Covers	Yes
Outlet Orientation	Single row of 4
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Input Cord Length (m)	4.572
Voltage Compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	No power switch
PHYSICAL	
Unit Dimensions (hwd / in.)	1.5 x 13.75 x 2.5
Unit Dimensions (hwd / cm)	3.8 x 34.9 x 6.4
Unit Weight (lbs.)	3.2
Unit Weight (kg)	1.5
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Yes
Receptacle Color	White
Color (AC Line Cord)	White
Outlets Measurement (Center to Center)	92mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 261.92mm; Distance between end tabs = 334.01mm
CERTIFICATIONS	
Approvals	TUV tested to UL 60601-1 and UL 60950-1 (USA); TUV tested to CAN/CSA-C22.2 No. 601.1-M90 and 60950-1-03 (Canada)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.