

1.8kW Single-Phase Basic PDU, 120V Outlets (14 5-15R), 5-15P, 15ft Cord, 0U Vertical

MODEL NUMBER: PDU1415



Description

Tripp Lite Basic Power Distribution Units / PDU systems offer reliable rackmount power distribution. Supplies equipment with continuous power from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

Features

- 15A single phase 120V Basic Power Distribution Unit / PDU
- Attached NEMA 5-15P 15A 120V input plug with 15 ft. / 4.5m line cord
- 0U, 24 in / 61cm vertical form factor supports installation in 2 or 4 post equipment racks
- Toolless mounting supported in button-mount compatible racks, plus nut-and-bolt mounting brackets for other mounting applications

Highlights

- Basic single phase 15A 120V PDU
- 0U vertical rackmount installation
- NEMA 5-15P input; 15 ft. / 4.5m line cord
- 14 NEMA 5-15R outlets
- 24 in. / 61cm housing

Applications

- Multi-outlet power distribution unit is the ideal means of powering multiple loads in racks, wallmount and other applications, such as internetworking, PC systems, telecommunications, audio/video, security, sound reinforcement and more. Ideal for distribution of UPS, generator or commercially derived AC power to protected equipment.

Package Includes

- PDU1415
- Instruction manual with warranty information

Specifications

OVERVIEW	
Style	Rackmount, Vertical Rackmount, Wallmount/Under-Counter
PDU Type	Basic
OUTPUT	
Output Capacity Details	1.8kW (120V), 1.9kW (127V), 1.5kW (100V); 15A maximum
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(14) 5-15R
Output Nominal Voltage	100-127V nominal, single phase
Overload Protection	15A breaker



Outlet Type	NEMA 5-15R
INPUT	
PDU Input Voltage	100; 120; 127
Maximum Input Amps	15
PDU Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Input Phase	Single-Phase
LEDS ALARMS & SWITCHES	
Switches	No power switch
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.75 x 27.25 x 8.25
Shipping Dimensions (hwd / cm)	7 x 69.2 x 21
Shipping Weight (lbs.)	5.2
Shipping Weight (kg)	2.4
Unit Dimensions (hwd / in.)	1.75 x 24 x 1.71
Unit Dimensions (hwd / cm)	4.45 x 61 x 4.34
Unit Weight (lbs.)	4.6
Unit Weight (kg)	2.1
Material of Construction	Metal
Form Factors Supported	0U vertical rackmount, wall-mount
PDU Form Factor	Vertical (0U)
ENVIRONMENTAL	
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	5 to 95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
SPECIAL FEATURES	
TVSS Grounding	Grounding lug
CERTIFICATIONS	
Certifications	Tested to UL60950-1 (USA) and CAN/CSA C22.2 No. 60950-1-03 (Canada)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.