

NOT for Patient-Care Rooms - UL1363 Power Strip with 6 Hospital-Grade Outlets, 15-ft. Cord

MODEL NUMBER: **PS-615-HG**



Description

Tripp Lite's PS-615-HG Power Strip offers 15A capacity AC power distribution in a rugged all-metal outlet strip for 120V applications. Features 6 hospital grade-receptacles, 15-ft. AC power cord and built-in resettable circuit breaker. Switchless design prevents accidental shutoff. Optional-use keyhole mounting tabs and flanges.

PLUG/OUTLETS: NEMA 5-15P-HG hospital-grade plug and 6 NEMA 5-15R-HG hospital-grade receptacles

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: All-metal corded multi-outlet strip

Features

- Rugged all-metal housing withstands years of use without breakage
- 6 x NEMA 5-15R-HG hospital-grade output receptacles
- 15-ft. AC cord with integrated, molded NEMA 5-15P-HG hospital-grade plug
- Optional-use keyhole mounting tabs and flanges.
- Switchless design prevents accidental shutoff
- 15A electrical capacity with built-in resettable circuit breaker
- 120V, 50/60Hz electrical compatibility
- Certified by UL (USA) and cUL (Canada)

Highlights

- Versatile power distribution strip
- 6 hospital-grade receptacles and hospital-grade plug
- 15-ft. cord
- 15A resettable circuit breaker

Applications

- AC power distribution with hospital-grade receptacles and plug where durability and reliability are required.
- Not for use where NEC requires hospital-grade receptacles.

Package Includes

- PS-615-HG Power Strip
- User manual with warranty information

Specifications

OVERVIEW	
Style	Strip
Model Type	NOT For Patient Areas



OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	15A circuit breaker
Outlet Orientation	Single row of 6
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Input Cord Length (m)	4.572
Voltage Compatibility (VAC)	120
LEDS ALARMS & SWITCHES	
Switches	No power switch
PHYSICAL	
Unit Dimensions (hwd / in.)	1.5 x 13.75 x 2.5
Unit Dimensions (hwd / cm)	3.8 x 34.9 x 6.4
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs and flanges enable mounting to a variety of surfaces
Receptacle Color	White
Color (AC Line Cord)	White
Outlets Measurement (Center to Center)	38.7mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole slots = 261.92mm; Distance between end tabs = 330.17mm
CERTIFICATIONS	
UL1363 (Power Tap)	UL1363 (Series Number: AGIB12015SL)
cUL / CSA (Canada)	cUL (Series Number: AGIB12015SL)
WARRANTY	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	Lifetime limited warranty
-------------------------------------	---------------------------

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.