

2U rack/console component power center w/ digital IR remote for all audio/video components - Isobar Audio/Video Power Center

MODEL NUMBER: HT1210ISOCTR



Description

Tripp Lite's HT1210ISOCTR Isobar Audio/Video Power Center provides ultimate protection 5700 joules stopping damaging surges and filtering disruptive EMI/RFI line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio; and longer component life spans. Perfect for large home/business theater installations, high-definition TVs, PVRs, satellite and A/V receivers, subwoofers, DVD/CD players and more. Exclusive Isolated Filter Banks eliminate noise interference between components. Features 12 AC outlets arranged in 3 filter banks: Analog, Digital and High Frequency. Four AC outlets are sequenced and individually controllable; IR remote control device included. Dual digital LED displays plus 12 additional LEDs show incoming voltage, current connected equipment load and a variety of operating conditions. Three-line 2.2 GHz HD-compatible gold coaxial surge protection, 1-line tel/modem protection with built-in splitter (1 line in/2 lines out) and 1-line Ethernet protection safeguard audio/video components on all connections. Metal housing; 2U rackmount/console design with included hardware and removable console feet, 10-ft. power cord with right-angle plug. Includes 6-ft. gold coaxial cable, 6-ft. phone cable and 6-ft. network cable. \$150,000 Ultimate Lifetime Insurance coverage (USA/Canada only).

Features

- 5700-joule surge suppression rating with EMI/RFI line noise filtering helps components perform at their peak (sharper, crisper video; deeper, fuller audio; and longer component life spans)
- Exclusive Isolated Filter Banks eliminate interference between connected components
- 3 built-in filter banks: Analog, Digital, High Current
- Metal housing safely withstands the strongest surges
- 12 surge-protected NEMA 5-15R AC outlets safeguard all audio/video components
- 4 sequenced, individually IR-controllable AC outlets work with either included remote device or with user-supplied universal learning IR remote to facilitate orderly system startup and shutdown
- 3 sets of surge-protected, HD-compatible 2.2 GHz Type F gold coaxial connectors safeguard components on cable, satellite and antenna connections;

Highlights

- 12 AC outlets arranged in three filter banks; 10-ft. power cord
- 4 sequenced, individually controllable AC outlets; IR remote control device included
- 5700-joule surge suppression rating
- 3-line 2.2GHz HD-compatible gold coaxial surge protection
- 1-line tel/modem surge protection with built-in splitter; 1-line Ethernet surge protection
- \$150,000 Ultimate Lifetime Insurance (USA/Canada only)

Applications

- Large home/business theater installations, high-definition TVs, PVRs, satellite and A/V receivers, subwoofers, DVD/CD players and more

Package Includes

- HT1210ISOCTR Isobar Audio/Video Power Center
- One hand-held IR remote control device; one 6-ft. gold coaxial cable; one 6-ft. phone cable; one 6-ft network cable
- Color-coordinated outlet/plug labels
- Hardware for 2U rackmounting
- Instruction manual with warranty information



one 6-ft. gold coaxial cable included

- 1-line tel/modem surge protection safeguards personal video recorders (PVRs) on a single dial-up connection. Built-in splitter (1 jack in/2 jacks out) allows simultaneous connection of two devices sharing a single line; one 6-ft. phone cable included
- 1-line Ethernet surge protection safeguards equipment on a 10/100 Base T network connection; one 6-ft network cable included
- 10-ft. power cord with right-angle NEMA 5-15P plug permits convenient placement anywhere within a home/business theater system
- 2 digital LED displays and 12 additional diagnostic LEDs alert user to input voltage levels, component load levels and 4 operational conditions (power, protection, grounding, selected outlets)
- 2U rackmount or console installation options; rackmount hardware and removable rubber console feet included
- Illuminated master switch provides one-touch power control over all components
- 15A circuit breaker protects against dangerous system overload
- Fail-safe thermal fusing acts like an additional circuit breaker, shutting down the unit and connected equipment in the event of a catastrophic surge
- Audible alarm immediately alerts user to damaged protection circuitry; perfect for installations where LEDs aren't normally viewed
- Color-coordinated outlet/plug labels match outlets to component power cords for easy identification
- TUV tested to UL standards 1449, 60950 and 962A
- \$150,000 Ultimate Lifetime Insurance covers connected components against surge damage for life! (USA/Canada only)

Specifications

OVERVIEW	
Style	Rack/Console
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1440
Circuit Breaker (amps)	12
Overload Protection	15A circuit breaker
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Plug Features	Right-angle plug
Input Cord Length (ft.)	10
Input Cord Length (m)	3
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	225000
LEDS ALARMS & SWITCHES	



Audible Alarm	Audible alarm
Switches	Illuminated on/off power switch
Diagnostic LEDs	Dual digital LED displays and 12 additional diagnostic LEDs alert user to input voltage levels, component load levels and 4 operational conditions (power, protection, grounding, selected outlets)
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	5700
AC Suppression Response Time	NM = instantaneous CM = < 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Safe Thermal Fusing	Yes
UL1449 Let Through Rating	330V - UL verified
EMI / RFI Filtering	Yes
Isolated Filter Banks	3
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	Yes
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	Yes
Cable (Coax) Protection Details	3 line (2.2 GHz Bandwidth)
Network (Ethernet) Protection	Yes
PHYSICAL	
Shipping Dimensions (hwd / in.)	7.5 x 21.5 x 15.0
Shipping Dimensions (hwd / cm)	19.1 x 54.6 x 38.1
Shipping Weight (lbs.)	16
Shipping Weight (kg)	7.3
Unit Dimensions (hwd / in.)	3.5 x 17.5 x 12
Unit Dimensions (hwd / cm)	8.8 x 43.8 x 30.5
Unit Weight (lbs.)	13.5
Unit Weight (kg)	6.1
Material of Construction	Metal
Included Mounting Accessories	2U rackmounting hardware
Receptacle Color	Black
Color (AC Line Cord)	Black
Form Factors Supported	2U rackmount/console installation
SPECIAL FEATURES	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Right-Angle Plug	Yes
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449
UL1283 (EMI Filter)	UL1283
cUL / CSA (Canada)	cUL
Approvals	RoHS, TUV tested to UL standards 1449 & 962A
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.