

Protect It! Surge Protector with 4 Side-Mounted Outlets , Direct Plug-In, 670 Joules

MODEL NUMBER: TLP4BK



Description

The TLP4BK Surge Suppressor from Tripp Lite has 4 side-mounted outlets (including 2 transformer-friendly outlets), a convenient direct plug-in design and diagnostic LEDs. The unit has a surge suppression rating of 670 joules to handle the strongest surges. \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

Features

- 4 side-mounted outlets allows easier plug connection and removal (including 2 transformer-friendly outlets)
- Direct plug-in design converts two outlets into four by plugging in to any wall outlet
- Surge suppression rating: 670 joules
- EMI/RFI noise filtering
- Diagnostic LEDs indicate protection present & ground present
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment

Specifications

| OVERVIEW | |
|---------------------------|-----------------------------|
| Style | Direct Plug-in |
| OUTPUT | |
| Frequency Compatibility | 50 / 60 Hz |
| Output Receptacles | (4) 5-15R |
| Circuit Breaker (amps) | 15 |
| Transformer Accommodation | Accommodates 2 transformers |

Highlights

- 4 side-mounted outlets (including 2 transformer-friendly outlets)
- Direct plug-in design
- 670 joule rating
- Diagnostic LEDs
- \$10,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Applications

- Computers, printers/peripherals, home electronics (stereos, TV, DVD player, etc.), satellite systems, appliances, power tools, lighting and more

Package Includes

- TLP4BK Surge Suppressor
- Instruction manual with warranty information



| | |
|------------------------------------|---|
| Outlet Orientation | Side-mounted |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 120V (110-125V) |
| Input Connection Type | NEMA 5-15P |
| Input Cord Length (ft.) | 0 |
| Input Cord Length Details | Direct plug-in |
| Voltage Compatibility (VAC) | 120 |
| LEDS ALARMS & SWITCHES | |
| Diagnostic LEDs | Built-in LEDs confirm suppressor "protection" (green) and "grounded" (red) status |
| SURGE / NOISE SUPPRESSION | |
| AC Suppression Joule Rating | 670 |
| AC Suppression Response Time | < 1 ns |
| Protection Modes | Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression |
| Clamping Voltage (RMS) | 330 |
| UL1449 Let Through Rating | 500V |
| EMI / RFI Filtering | Up to 20 dB |
| DATALINE SURGE SUPPRESSION | |
| Telephone/DSL Protection | No |
| Cable (Coax) Protection | No |
| Network (Ethernet) Protection | No |
| PHYSICAL | |
| Shipping Dimensions (hwd / in.) | 9.44 x 5.75 x 2.15 |
| Shipping Dimensions (hwd / cm) | 23.98 x 14.61 x 5.46 |
| Shipping Weight (lbs.) | 0.38 |
| Shipping Weight (kg) | 0.17 |
| Unit Dimensions (hwd / in.) | 3.26 x 5.80 x 1.86 |
| Unit Dimensions (hwd / cm) | 8.28 x 14.73 x 4.72 |
| Unit Weight (lbs.) | 0.36 |
| Unit Weight (kg) | 0.16 |
| Material of Construction | Plastic |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|---|
| Housing Color | Black |
| Receptacle Color | Black |
| Outlets Measurement (Center to Center) | Distance between transformer outlets = 56mm; Distance between standard outlets = 28mm |
| CERTIFICATIONS | |
| UL1449 3rd Edition (AC Suppression) | UL1449 with fail safe circuit |
| FCC Part 68 (Communications) | Yes |
| cUL / CSA (Canada) | cUL |
| Approvals | RoHS |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |
| Connected Equipment Insurance (U.S., Canada & Puerto Rico) | \$10,000 Ultimate Lifetime Insurance |

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.