



375W PowerVerter Ultra-Compact Car Inverter with 2 Outlets

MODEL NUMBER: PV375



Description

Utilize your vehicle's battery to efficiently power office equipment on the road. Continuously supplies up to 375 watts of 120V AC power to 2 AC outlets from any 12V battery or automotive DC source. Convenient cigarette lighter DC input jack with 3-ft. cable provides 1-step installation. Portable and compact, the inverter's design is among the most rugged available thanks to its lightweight metal casing.

Features

- Allows users to run AC devices from any 12V cigarette lighter socket
- Converts 12V DC battery power to 120V AC power
- 375 watts continuous output power; 600 watts peak output power (instantaneous)
- 2 outlets
- 3-ft. cord with cigarette lighter plug
- Ultra compact, lightweight design with all-metal housing
- Low battery alarm with auto-shutoff preserves vehicle battery
- Overload alarm with auto-shutoff prevents wattage overload
- Replaceable 40amp fuse protects inverter from overload
- Lighted power switch

Specifications

OVERVIEW	
Style	Compact
Model Type	Inverters

Highlights

- 12V DC input; 120V AC output; 2 outlets
- 375 watts continuous output
- 600 watts peak output (instantaneous)
- Convenient cigarette lighter plug

Applications

- Ideal for laptop computers, portable electronics, battery chargers for cell phones, notepads, game systems, personal printers and battery rechargers for small battery-operated power tools, portable TV-VCR-stereo systems, camcorders, lighting and other low-power applications under 375 watts.

Package Includes

- PV375 Inverter
- Warranty information
- Instruction manual



OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(2) 5-15R
Output (Watts)	375
Continuous Output Capacity (Watts)	375
Peak Output Capacity (Watts)	600
Output Nominal Voltage	120V
Output Voltage Regulation	Maintains PWM sine wave output voltage of 115 V AC (+/- 8 V AC)
Output Frequency Regulation	60 Hz (+/- 3 Hz)
Overload Protection	40A automotive input fuse
INPUT	
Maximum Input Amps / Watts	Full continuous load - 40A at 12V DC, No load - 0.65A at 12V DC
Input Connection Type	12V DC cigarette lighter input plug connection
Input Cord Length Details	3 ft. hardwire input cable, 16 gauge, 2 wire
Voltage Compatibility (VDC)	12
BATTERY	
DC System Voltage (VDC)	12
LEDS ALARMS & SWITCHES	
Audible Alarm	Dual function alarm indicates overload conditions or low DC input voltage of 10.5V or less.
Switches	Lighted on/off power switch
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.5 x 11.75 x 7.5
Shipping Dimensions (hwd / cm)	6.35 x 29.85 x 19.05
Shipping Weight (lbs.)	2.5
Shipping Weight (kg)	1.1
Unit Dimensions (hwd / in.)	2 x 4.25 x 7
Unit Dimensions (hwd / cm)	5.08 x 10.8 x 17.78
Unit Weight (lbs.)	2.3
Unit Weight (kg)	1
Cooling Method	Fan
Material of Construction	Aluminum / sheet metal



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

ENVIRONMENTAL	
Relative Humidity	0-95% non-condensing
SPECIAL FEATURES	
Remote Control Capability	No
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.