

## Eco-Surge 6-Outlet Surge Protector, 6-ft. Cord, 1080 Joules, Individually-Controlled

MODEL NUMBER: TLP76MSG



### Description

Tripp Lite's TLP76MSG offers reliable, GREEN surge technology that protects your computer and peripherals as well as the environment and your wallet. Energy-saving outlet configuration reduces energy waste (phantom loads) by cutting AC power to unused peripherals. The TLP76MSG has one always on outlet for those peripherals that need constant power like a fax machine, DVR or router. It also offer convenient, individual outlet switches that allow users to select which device is turned on and off. The TLP76MSG has 7 total outlets, 6 foot cord and diagnostic LEDs to warn of wiring problems and suppressor damage. Network-grade AC suppression rated at 1080 joules shields equipment from surges and line noise. Designed with an attractive cool gray suppressor housing, the TLP76MSG can accommodate up to 4 transformer plug outlets offering convenient protection of desktop computer equipment and accessories. \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

### Features

- Energy-saving green outlets allow individual outlet control using illuminated power switches for cutting power to peripherals not in use.
- Six green outlets have their own illuminated ON/OFF switch for cutting power to peripherals when they are not in use. One "Always On" outlet provides continuous power for devices such as DVRs (TiVo), cable and satellite boxes, modems, routers and fax machines.
- In addition to the individual illuminated outlet switches, an illuminated Master Switch controls power to all outlets (except the Always On outlet) at once. It can override other "ON" settings to cut power to all switched outlets at once.
- Protected (Green) LED assures protection is present & Always On (Red) LED indicates that the Always On outlet is receiving power.
- 1080 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans).
- .

### Highlights

- Individual outlet control
- 1080 joules
- 7 outlet / 6-ft cord
- Diagnostic LEDs
- \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

### Applications

- Ideal for any desktop, network or home computing application requiring AC protection

### Package Includes

- TLP76MSG ECO-SURGE Home/Business Theater Surge Suppressor
- Instruction manual with warranty information

## Specifications

OVERVIEW	
Style	Strip



<b>OUTPUT</b>	
Output Volt Amp Capacity (VA)	120
Output Watt Capacity (Watts)	1800
Frequency Compatibility	60 Hz
Output Receptacles	(7) 5-15R
Outlet Type	NEMA 5-15R
Transformer Accommodation	Supports 1 large transformer without covering remaining outlets, accepts up to 4 transformers total
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMAP - NEMA5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Input Cord Gauge Type	14 AWG, 3 COND, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	72000
<b>LEDS ALARMS &amp; SWITCHES</b>	
LED Indicators	Protected (Green)" & Always On Receptacle (Red)
Switches	1 x Lighted Master Switch & 6 x Lighted Receptacle Switches
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression.
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400v
EMI / RFI Filtering	Up to 40dB
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	No
<b>PHYSICAL</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

Shipping Dimensions (hwd / in.)	17.2 x 4.24 x 2
Shipping Dimensions (hwd / cm)	43.69 x 10.77 x 5.08
Shipping Weight (lbs.)	1.76
Shipping Weight (kg)	0.80
Unit Dimensions (hwd / in.)	1.40 x 3.40 x 15
Unit Dimensions (hwd / cm)	3.56 x 8.64 x 38.1
Unit Weight (lbs.)	1.54
Unit Weight (kg)	0.70
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting slots enable wall mounting
Color (AC Line Cord)	Cool Gray
<b>SPECIAL FEATURES</b>	
Green Energy-Saving Features	Individually controllable outlets
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 Ultimate Lifetime Insurance

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.