



EcoClassic Candle B35

EcoClassic 42W E14 240V B35 CL 1CT

Philips EcoClassic Candle light bulbs offer the classical shape you are used to, but with better energy efficiency. This new 'classic' gives high-quality light, is dimmable and starts immediately.

Product data

• General Characteristics

Cap-Base	SES
Bulb	B35 [B 35mm]
Bulb Finish	Clear
Burning Position	any [Any/Universal]
Nominal Lifetime	2000 hr
Rated Lifetime	2000 hr
Rated Lifetime (years)	2 an

• Light Technical Characteristics

Colour Rendering Index	100 Ra8
Colour Temperature	2800 K
Colour Temperature Technical	2800 K
Lamp Luminous Flux	630 Lm
Rated Luminous Flux	630 Lm
Lamp Luminous Efficacy	15.0 Lm/W
LLMF - end nominal lifetime	80 (min) %

• Electrical Characteristics

Rated Wattage	42.0 W
Lamp Wattage	42 W
Technical Lamp Power	42 W
Power Factor	1 -
Voltage	240 V
Lamp Current	0.18 A
Dimmable	yes
Wattage Equivalent	55 W
Starting Time	0.0 s

Warm-up Time to 60% Light Outp	instant full light
--------------------------------	--------------------

• Environmental Characteristics

Energy Efficiency Label (EEL)	D
Energy consumption kWh/1000h	42 kWh

• Measuring Conditions

Switching cycle	8000X
-----------------	-------

• Luminaire Design Requirements

Cap-Base Temperature	130 (max) C
----------------------	-------------

• Product Dimensions

Overall Length C	99.2 (max) mm
Diameter D	36 (max) mm

• Product Data

Order code	820621 00
Full product code	872790082062100
Full product name	EcoClassic 42W E14 240V B35 CL 1CT
Order product name	EcoClassic 42W E14 240V B35 CL 1CT/15
Pieces per pack	1
Packing configuration	15
Packs per outerbox	15
Bar code on pack - EAN1	8727900820621

PHILIPS

EcoClassic Candle B35


Bar code on
outerbox - EAN3
Logistic code(s) -
12NC

8727900820638

925646345501


Net weight per piece 18.400 gr

Dimensional drawing



EcoClassic 42W E14 240V B35 CL 1CT

Product	C (Max)	D (Max)
EcoCl30 42W E14 240V B35 CL	99.2	36



E14



© 2014 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2014, April 17
data subject to change